



FlexScape Inground IL9

Inground (IL9), IL9DC-A, Composite, 10W, 12V, Wide

Inground (IL9), IL9DC-A, Composite, 10W, 12V, Wide

Philips Hadco FlexScape LED inground luminaire IL9 opens new horizons for low-voltage landscape lighting. It is designed for optimal LED performance and superior flexibility. The luminaire creates visual interest for pathways, walls, columns and foliage. Its rugged housing installs directly into the soil. In addition to low-energy outdoor lighting, it features convenient on-site beam adjustability. This allweather luminaire comes with 100% molded silicone gaskets.

Product data

General Information	
Lamp Source Code	LED
Lamp Watts	10
Color Temperature	4000K
CRI	70
Operating and Electrical	
Luminaire Input Watts	10
Voltages	12 V
Initial Performance (IEC Compliant)	
Luminaire Lumens	606

Product Data	
Order product name	Inground (IL9), IL9DC-A, Composite, 10W, 12V, Wide
Commercial Code	IL9
Order code	IL9
Catalog Number Description	Inground (IL9), IL9DC-A, Composite, 10W, 12V, Wide
Service / Spec Smart	-
Material Nr. (12NC)	HAD70000422