



RSB2 Step Light

Step Light, Polycarbonate, 18W CFL, 120V, Shroud

Step Light, Polycarbonate, 18W CFL, 120V, Shroud

The RSB2 is a polycarbonate step light for line voltage applications. It includes an aluminum back box for concrete and brick applications. The optical assembly consists of a UV stabilized, injection molded polycarbonate bubble faceplate reinforced with frosted tempered glass. A symmetric Reflector is precision formed, semi-specular aluminum or highly polished aluminum, which produces a wide symmetric distribution for general area lighting. Lamping choices include PLC, CFL and incandescent.

Product data

General Information	
Lamp Source Code	CFL
Lamp Watts	18
Operating and Electrical	
Voltages	120 V
Product Data	
Order product name	Step Light, Polycarbonate, 18W CFL, 120V, Shroud

Commercial Code	RSB2
Order code	RSB2
Catalog Number Description	Step Light, Polycarbonate, 18W CFL, 120V, Shroud
Service / Spec Smart	-
Material Nr. (12NC)	HAD70000979