



# Pima LED pendant - small (CXF6)

## Small Pima LEDGINE, 32 LED, Type II, Flat Glass Lens

Small Pima LEDGINE, 32 LED, Type II, Flat Glass Lens - 117 lm/W

The Philips Hadco Pima pendant family offers a simple modern take on the traditional pendant lantern, providing style and elegance to downtown areas, commercial developments, parks and residential communities. These pendants use the latest LED technology which maximizes energy savings and provides uniform and comfortable light. The Swan is a great solution for new installations or replacing a variety of HID sources.

### Product data

General Information	
Lamp Source Code	LED
Colour Temperature	4000K
Photometric Distribution Type	Type II
Operating and Electrical	
Luminaire Input Watts	35
Voltages	120/208/240/277/347/480 V
Initial Performance (IEC Compliant)	
Luminaire Lumens	4134

Efficacy	117 lm/W
Product Data	
Order product name	Small Pima LEDGINE, 32 LED, Type II, Flat Glass Lens
Commercial Code	CXF632-G2-2N3-16
Order code	CXF632-G2-2N3-16
Catalog Number Description	Small Pima LEDGINE, 32 LED, Type II, Flat Glass Lens
Service / Spec Smart	-
Material Nr. (12NC)	HAD800030604