



Refractive post top with LumiLock LED (RL34/RL54)

LumiLock LED - GX4, 64 LED, Type V Config,Wide Optical, @200 mA

LumiLock LED - GX4, 64 LED, Type V Config,Wide Optical, @200 mA - 77 lm/W

Whether you are looking to beautify or add a sense of security and wellbeing to your outdoor space, the highly configurable Philips Hadco LED refractive post tops paired with the latest LumiLock light engine GX4 will definitely help you achieve your goals. A multitude of exterior luminaire styles allow you to create promenades and areas exuding timeless, historical charm both day and night. The configurable LED light engine GX4 is an ideal alternative to HID sources, providing you with significant energy savings, and more choices for light levels, optics and controls.

Product data

General Information		Initial Performance (IEC Compliant)	
Lamp Watts	39	Luminaire Lumens	3024
Color Temperature	3000K	Efficacy	77 lm/W
CRI	70	Product Data	
Photometric Distribution Type	Type V	Order product name	LumiLock LED - GX4, 64 LED, Type V Config,Wide Optical, @200 mA
Operating and Electrical		Commercial Code	RL54xDxxxxWxxWx2xxxxx-GX4
Voltages	120/208/240/277/347/480 V	Order code	RL54xDxxxxWxxWx2xxxxx-GX4

Refractive post top with LumiLock LED (RL34/RL54)

Catalog Number	Description
	LumiLock LED - GX4, 64 LED, Type V Config,Wide Optical, @200 mA
Service / Spec Smart	-

Material Nr. (12NC)	HAD800031169
---------------------	--------------

