



Refractive post top with LumiLock LED (RL34/RL54)

LumiLock LED - GX4, 64 LED, Type V Config, Wide Optical, @530 mA

LumiLock LED - GX4, 64 LED, Type V Config, Wide Optical, @530 mA - 69 lm/W

Whether you are looking to beautify or add a sense of security and wellbeing to your outdoor space, the highly configurable Philips Hadco LED refractive post tops paired with the latest LumiLock light engine GX4 will definitely help you achieve your goals. A multitude of exterior luminaire styles allow you to create promenades and areas exuding timeless, historical charm both day and night. The configurable LED light engine GX4 is an ideal alternative to HID sources, providing you with significant energy savings, and more choices for light levels, optics and controls.

Product data

General Information	
Lamp Watts	103
Color Temperature	3000K
CRI	70
Photometric Distribution Type	Type V
Operating and Electrical	
Voltages	120/208/240/277/347/480 V

Initial Performance (IEC Compliant)	
Luminaire Lumens	7251
Efficacy	69 lm/W
Product Data	
Order product name	LumiLock LED - GX4, 64 LED, Type V Config, Wide Optical, @530 mA
Commercial Code	RL54xDxxxxWxxWx5xxxx-GX4
Order code	RL54xDxxxxWxxWx5xxxx-GX4

Refractive post top with LumiLock LED (RL34/RL54)

Catalog Number	Description
	LumiLock LED - GX4, 64 LED, Type V Config,Wide Optical, @530 mA

Material Nr. (12NC)	HAD800031172
----------------------------	--------------

Service / Spec Smart	-
-----------------------------	---

