



RSF2 Step Light LED

Step Light, 4.3W LED, 120V, 4K, Frosted

Step Light, 4.3W LED, 120V, 4K, Frosted

The RSF2 is a line voltage step light perfect for high pedestrian traffic and plant life applications. It is available in standard sources including CFL along with high brightness LED sources. The RSF2 is available with a die-cast aluminum back box and has polycarbonate, color impregnated, dark bronze finish. The optical assembly includes opal lens made of UV stabilized injection molded polycarbonate as well as a warm lens. Available in black and bronze. Symmetric Reflector is specular aluminum formed Reflector.

Product data

General Information	
Lamp Source Code	LED
Color Temperature	4000K
CRI	70
Operating and Electrical	
Luminaire Input Watts	4
Voltages	120 V

Product Data	
Order product name	Step Light, 4.3W LED, 120V, 4K, Frosted
Commercial Code	RSF2
Order code	RSF2
Catalog Number Description	Step Light, 4.3W LED, 120V, 4K, Frosted
Service / Spec Smart	-
Material Nr. (12NC)	HAD800032063