



Stockholm (53000 Series)

Stockholm, 100 HPS, Type III Glass Refractor

Stockholm, 100 HPS, Type III Glass Refractor

The Philips Hadco Stockholm post top family offers a simple modern take on the traditional lantern, providing style and elegance to downtown areas, commercial developments, parks and residential communities. The Stockholm offers a range of optical distributions and panel globes to suite any application.

Product data

| General Information | |
|-------------------------------|--|
| Lamp Source Code | HPS |
| Lamp Watts | 100 |
| Photometric Distribution Type | Type III |
| Operating and Electrical | |
| Voltages | 120/208/240/277 V |
| Product Data | |
| Order product name | Stockholm, 100 HPS, Type III Glass Refractor |

| | |
|----------------------------|--|
| Commercial Code | 53630 Type III |
| Order code | 53630 Type III |
| Catalog Number Description | Stockholm, 100 HPS, Type III Glass Refractor |
| Service / Spec Smart | - |
| Material Nr. (12NC) | HAN00001278 |