



Mini Wallcube

Type IV - Wallcube, Spec Grade Security light, cast aluminum housing, borosilicate glass lens, Tritap voltage

Type IV - Wallcube, Spec Grade Security light, cast aluminum housing, borosilicate glass lens, Tritap voltage

The Keene Maxi/Mini Series represents the industry standard for durability and performance. This series is a good choice for perimeter security lighting, area parking lots, schools, warehouses/plants, architectural lighting, above loading docks, apartments, condos and overpasses. Rugged die cast aluminum construction ensures long life, and our bronze Duraplex IITM electrostatic powder finish resists fading, chipping, peeling and cracking. Deep die cast fins provide maximum heat dissipation, cooler operation and longer electrical component life. Heavy heat and shock resistant borosilicate glass, in combination with an optional polycarbonate shield or wire guard makes these fixtures impervious to vandalism.

Product data

General Information	
Lamp Source Code	MH
Lamp Watts	100
Lamp Envelope Code	BT/ED/E-17
Number of Lamps	1
Photometric Distribution Type	Type IV
Mounting	Wall
Operating and Electrical	
Voltages	120/277/347 V

Mechanical and Housing	
Shape	Rectangular
Product Data	
Order product name	Type IV - Wallcube, Spec Grade Security light, cast aluminum housing, borosilicate glass lens, Tritap voltage
Commercial Code	313100MAL-T
Order code	313100MAL-T
Catalog Number Description	Type IV - Wallcube, Spec Grade Security light, cast aluminum housing, borosilicate glass lens, Tritap voltage
Material Nr. (12NC)	KEE7000312

Mini Wallcube

