



# Mini Wallcube

Type IV - Wallcube, Spec Grade Security light, cast aluminum housing, borosilicate glass lens, Tritap voltage

Type IV - Wallcube, Spec Grade Security light, cast aluminum housing, borosilicate glass lens, Tritap voltage

The Keene Maxi/Mini Series represents the industry standard for durability and performance. This series is a good choice for perimeter security lighting, area parking lots, schools, warehouses/plants, architectural lighting, above loading docks, apartments, condos and overpasses. Rugged die cast aluminum construction ensures long life, and our bronze Duraplex IITM electrostatic powder finish resists fading, chipping, peeling and cracking. Deep die cast fins provide maximum heat dissipation, cooler operation and longer electrical component life. Heavy heat and shock resistant borosilicate glass, in combination with an optional polycarbonate shield or wire guard makes these fixtures impervious to vandalism.

## Product data

General Information	
Lamp Source Code	HPS
Lamp Watts	150
Lamp Envelope Code	BT/ED/E-17
Number of Lamps	1
Photometric Distribution Type	Type IV
Mounting	Wall
Operating and Electrical	
Voltages	120/277/347 V

Mechanical and Housing	
Shape	Rectangular
Product Data	
Order product name	Type IV - Wallcube, Spec Grade Security light, cast aluminum housing, borosilicate glass lens, Tritap voltage
Commercial Code	313150LXL-T
Order code	313150LXL-T
Catalog Number Description	Type IV - Wallcube, Spec Grade Security light, cast aluminum housing, borosilicate glass lens, Tritap voltage
Service / Spec Smart	Service Smart (2 Days) Canada
Material Nr. (12NC)	KEE7000315

