



# MicroSquare gen2 Suspended LED

MicroSquare gen2 Suspended Direct/Indirect LED,  
5900 lm/4ft, 3000/3500/4000K Direct/Indirect, Flush Silk  
Lens Down - Symmetric Wide-Throw Lens Up

MicroSquare gen2 Suspended Direct/Indirect LED, 5900 lm/4ft,  
3000/3500/4000K Direct/Indirect, Flush Silk Lens Down - Symmetric  
Wide-Throw Lens Up - 119 lm/W

Philips Ledalite's MicroSquare gen2 has been re-engineered to furnish your space with the highest quality, discreet, narrow lines of continuous light. Elegant, low glare illumination with wide-throw upper and lower distributions improve visual comfort while allowing increased fixture spacing. This in turn, helps reduce initial and operating costs.

## Product data

General Information	
Lamp Source Code	LED
Color Temperature	3000/3500/4000K
CRI	80
Photometric Distribution Type	Direct/Indirect
Mounting	Suspended
Operating and Electrical	
Luminaire Input Watts	49
Voltages	120/277/347 V

Mechanical and Housing	
Shape	Linear
Initial Performance (IEC Compliant)	
Luminaire Lumens	5900
Efficacy	119 lm/W
Product Data	
Order product name	MicroSquare gen2 Suspended Direct/Indirect LED, 5900 lm/4ft, 3000/3500/4000K Direct/Indirect, Flush Silk Lens Down - Symmetric Wide-Throw Lens Up
Commercial Code	2206LxBLQ
Order code	2206LxBLQ

# MicroSquare gen2 Suspended LED

Catalog Number	Description
	MicroSquare gen2 Suspended Direct/Indirect LED, 5900 lm/4ft, 3000/3500/4000K Direct/Indirect, Flush Silk Lens Down - Symmetric Wide-Throw Lens Up
Service / Spec Smart	-

Material Nr. (12NC)	LED04283
---------------------	----------

