



# TruGroove suspended

## TruGroove Suspended Direct LED, 2300 lm/4ft, 3000/3500/4000K Direct, Asymmetric MesoOptics Lens

TruGroove Suspended Direct LED, 2300 lm/4ft, 3000/3500/4000K Direct, Asymmetric MesoOptics Lens - 88 lm/W

TruGroove LED is driving performance beyond the edge. Innovative optics deliver exceptional uniformity and wide row spacing from a 3" aperture continuous line-of light. An extended family and refined design are perfect for lighting any professional space.

### Product data

General Information		Initial Performance (IEC Compliant)	
Lamp Source Code	LED	Luminaire Lumens	2300
Colour Temperature	3000/3500/4000K	Efficacy	88 lm/W
CRI	80		
Photometric Distribution Type	Direct	Product Data	
Mounting	Suspended	Order product name	TruGroove Suspended Direct LED, 2300 lm/4ft, 3000/3500/4000K Direct, Asymmetric MesoOptics Lens
Operating and Electrical		Order code	2901LxGWN
Voltages	120/277/347 V	Material Nr. (12NC)	LED04368
Luminaire Input Watts	24	Catalog Number	2901LxGWN
Mechanical and Housing		Catalog Number Description	TruGroove Suspended Direct LED, 2300 lm/4ft, 3000/3500/4000K Direct, Asymmetric MesoOptics Lens
Shape	Linear		