



TruGroove Surface LED

TruGroove Surface Direct LED, 3200 lm/4ft,
3000/3500/4000K Direct, Asymmetric MesoOptics Lens

TruGroove Surface Direct LED, 3200 lm/4ft, 3000/3500/4000K
Direct, Asymmetric MesoOptics Lens - 84 lm/W

TruGroove LED is driving performance beyond the edge. Innovative optics deliver exceptional uniformity and wide row spacing from a 3" aperture continuous line-of light. An extended family and refined design are perfect for lighting any professional space.

Product data

General Information	
Lamp Source Code	LED
Colour Temperature	3000/3500/4000K
CRI	80
Photometric Distribution Type	Direct
Mounting	Surface
Operating and Electrical	
Luminaire Input Watts	35.1
Voltages	120/277/347 V
Mechanical and Housing	
Shape	Linear
Initial Performance (IEC Compliant)	
Luminaire Lumens	3200

Efficacy	84 lm/W
Product Data	
Order product name	TruGroove Surface Direct LED, 3200 lm/4ft, 3000/3500/4000K Direct, Asymmetric MesoOptics Lens
Commercial Code	2911LxEWN
Order code	2911LxEWN
Catalog Number Description	TruGroove Surface Direct LED, 3200 lm/4ft, 3000/3500/4000K Direct, Asymmetric MesoOptics Lens
Service / Spec Smart	-
Material Nr. (12NC)	LED04389