



TruGroove Wall LED

TruGroove Wall Direct Asymmetric LED, 2300 lm/4ft,
3000/3500/4000K Direct, Asymmetric MesoOptics Lens

TruGroove Wall Direct Asymmetric LED, 2300 lm/4ft,
3000/3500/4000K Direct, Asymmetric MesoOptics Lens - 88 lm/W

TruGroove LED is driving performance beyond the edge. Innovative optics deliver exceptional uniformity and wide row spacing from a 3" aperture continuous line-of light. An extended family and refined design are perfect for lighting any professional space.

Product data

| | | | |
|--|-----------------|----------------------------|--|
| General Information | | Efficacy | |
| Lamp Source Code | LED | 88 lm/W | |
| Color Temperature | 3000/3500/4000K | Product Data | |
| CRI | 80 | Order product name | TruGroove Wall Direct Asymmetric LED, 2300 lm/4ft, 3000/3500/4000K Direct, Asymmetric MesoOptics Lens |
| Photometric Distribution Type | Direct | Commercial Code | 2921LxGWN |
| Mounting | Wall | Order code | 2921LxGWN |
| Operating and Electrical | | Catalog Number Description | TruGroove Wall Direct Asymmetric LED, 2300 lm/4ft, 3000/3500/4000K Direct, Asymmetric MesoOptics Lens |
| Luminaire Input Watts | 24 | Service / Spec Smart | - |
| Voltages | 120/277/347 V | Material Nr. (12NC) | LED04393 |
| Mechanical and Housing | | | |
| Shape | Linear | | |
| Initial Performance (IEC Compliant) | | | |
| Luminaire Lumens | 2300 | | |