



# TruGroove Recessed

## TruGroove Recessed Asymmetric LED, 2200 lm/4ft, 3000/3500/4000K Direct, Flush MesoOptics Lens

TruGroove Recessed Asymmetric LED, 2200 lm/4ft, 3000/3500/4000K Direct, Flush MesoOptics Lens - 90 lm/W

TruGroove Recessed delivers unrivaled performance and a truly innovative design – making a definitive statement in any architectural space. TruGroove Recessed corners provide endless opportunities for creative freedom with geometric patterns in walls and ceilings.

### Product data

General Information	
Color Temperature	3000/3500/4000K
CRI	80
Photometric Distribution Type	Asymmetric
Mounting	Recessed
Operating and Electrical	
Luminaire Input Watts	20.5
Voltages	120/277/347 V
Mechanical and Housing	
Shape	Linear
Initial Performance (IEC Compliant)	
Luminaire Lumens	2200

Efficacy	90 lm/W
Product Data	
Order product name	TruGroove Recessed Asymmetric LED, 2200 lm/4ft, 3000/3500/4000K Direct, Flush MesoOptics Lens
Commercial Code	3908LxGQ
Order code	3908LxGQ
Catalog Number Description	TruGroove Recessed Asymmetric LED, 2200 lm/4ft, 3000/3500/4000K Direct, Flush MesoOptics Lens
Service / Spec Smart	-
Material Nr. (12NC)	LED04549