



SilkSpace

SilkSpace 2'x2' LED, 1700 lm, 3000/3500/4000K Direct, Beam Shaping Light Guide with MesoOptics

SilkSpace 2'x2' LED, 1700 lm, 3000/3500/4000K Direct, Beam Shaping Light Guide with MesoOptics - 108 lm/W

Philips Ledalite SilkSpace LED recessed combines LED Light Guide technology and Ledalite's revolutionary MesoOptics technology to deliver discrete, comfortable lighting with great performance and ultra low-glare.

Product data

General Information		Efficacy	
Color Temperature	3000/3500/4000K	108 lm/W	
CRI	80		
Photometric Distribution Type	Direct		
Mounting	Recessed		
Operating and Electrical		Product Data	
Luminaire Input Watts	16.7	Order product name	SilkSpace 2'x2' LED, 1700 lm, 3000/3500/4000K Direct, Beam Shaping Light Guide with MesoOptics
Voltages	120/277/347 V	Commercial Code	4222DxxxL8xK
Mechanical and Housing		Order code	4222DxxxL8xK
Fixture Size	2 ft x 2 ft	Catalog Number Description	SilkSpace 2'x2' LED, 1700 lm, 3000/3500/4000K Direct, Beam Shaping Light Guide with MesoOptics
Shape	Square	Service / Spec Smart	-
Initial Performance (IEC Compliant)		Material Nr. (12NC)	LED04666
Luminaire Lumens	1700		