



Frame-In Kit 8 3/4"

Frame Lp 8 3/4" 2-18W QT 120/277V Elec

Frame Lp 8 3/4" 2-18W QT 120/277V Elec

The Calculite Vandal/Wet location downlights use the RotoLock™ technology. Just twist the die-cast ring into place. The sealed o-ring construction provides the wet location seal. A single screw locks the ring in place to prevent vandalism.

Product data

General Information	
Lamp Source Code	CFL
Lamp Watts	18/26
Lamp Envelope Code	Quad T
Number of Lamps	2
Downlight Type	Non-IC Frames
Mounting	Recessed franse vertaling
Operating and Electrical	
Maximum Lamp Watts	18
Voltages	120/277 V

Mechanical and Housing	
Aperture Size Code	8 3/4 in
Shape	Round
Product Data	
Order product name	Frame Lp 8 3/4" 2-18W QT 120/277V Elec
Commercial Code	8218LPF120
Order code	8218LPF120
Catalog Number Description	Frame Lp 8 3/4" 2-18W QT 120/277V Elec
Material Nr. (12NC)	LIGC00001304