



5" Lytecaster Reflector Trim

Grooved Baffle Black PAR-30

Grooved Baffle Black PAR-30

Step Baffle Wall Washer provides a high intensity, smooth wash of light up to the ceiling line. Dual reflector optics assure effective output with economical light sources while the aluminum step baffle reduces glare.

Product data

General Information		Shape	
Lamp Watts	50/75	Round	
Lamp Envelope Code	PAR-30		
Number of Lamps	1		
Downlight Type	Open Downlight		
Mounting	Recessed franse vertaling		
Operating and Electrical		Product Data	
Maximum Lamp Watts	75	Order product name	Grooved Baffle Black PAR-30
		Commercial Code	R620BK
		Order code	R620BK
		Catalog Number Description	Grooved Baffle Black PAR-30
		Service / Spec Smart	-
		Material Nr. (12NC)	LIGC00003701
Mechanical and Housing			
Aperture Size Code	5 1/4 in		