



Basic Track Heads

Basic Wall Washer R30 100W White

Basic Wall Washer R30 100W White

Basic Lytespan wall washer delivers an efficient, versatile cylinder with kick reflector gives smooth, broad wash of light from ceiling to floor without scalloping.

Product data

| General Information | |
|-------------------------------|------------|
| Lamp Envelope Code | R-30 |
| Number of Lamps | 1 |
| Photometric Distribution Type | Wide Flood |
| Mounting | Track |
| Operating and Electrical | |
| Voltages | 120 V |

| Product Data | |
|----------------------------|----------------------------------|
| Order product name | Basic Wall Washer R30 100W White |
| Commercial Code | 6310 |
| Order code | 6310 |
| Catalog Number Description | Basic Wall Washer R30 100W White |
| Service / Spec Smart | - |
| Material Nr. (12NC) | LIGU60000279 |