



# Basic Track Heads

Universal Black 150W PAR38 Cool Beam; 75W PAR16, 50W PAR20, 75W PAR30

Universal Black 150W PAR38 Cool Beam; 75W PAR16, 50W PAR20, 75W PAR30

Basic Lytespan wall washer delivers an efficient, versatile cylinder with kick reflector gives smooth, broad wash of light from ceiling to floor without scalloping.

## Product data

General Information	
Number of Lamps	1
Mounting	Track
Operating and Electrical	
Voltages	120 V
Product Data	
Order product name	Universal Black 150W PAR38 Cool Beam; 75W PAR16, 50W PAR20, 75W PAR30

Commercial Code	6322
Order code	6322
Catalog Number Description	Universal Black 150W PAR38 Cool Beam; 75W PAR16, 50W PAR20, 75W PAR30
Service / Spec Smart	-
Material Nr. (12NC)	LIGU60000280