



5" Lytecaster Reflector Trim

5" Basic Baffle White

5" Basic Baffle White

Step Baffle Wall Washer provides a high intensity, smooth wash of light up to the ceiling line. Dual reflector optics assure effective output with economical light sources while the aluminum step baffle reduces glare.

Product data

| General Information | |
|-------------------------------|---------------------------|
| Lamp Watts | 26 |
| Lamp Envelope Code | Triple T |
| Number of Lamps | 1 |
| Downlight Type | Open Downlight |
| Photometric Distribution Type | Direct |
| Mounting | Recessed franse vertaling |
| Mechanical and Housing | |
| Aperture Size Code | 5 in |
| Shape | Round |

| Product Data | |
|----------------------------|-----------------------|
| Order product name | 5" Basic Baffle White |
| Commercial Code | 1076WH |
| Order code | 1076WH |
| Catalog Number Description | 5" Basic Baffle White |
| Service / Spec Smart | - |
| Material Nr. (12NC) | LIGU60000869 |