



# Pendalyte 6.5"

## Pendalyte 6.5 Perf Satin Aluminum Reflector

### Pendalyte 6.5 Perf Satin Aluminum Reflector

Powerful downlighting for high ceiling spaces. Created in a range of light distributions, styles, lamps and wattages, Pendalytes™ meet the demanding needs of a variety of commercial and institutional applications including retail stores and supermarkets.

#### Product data

General Information	
Lamp Envelope Code	A-21
Lamp Watts	150
Number of Lamps	1
Mounting	Surface Cable Suspended
Operating and Electrical	
Maximum Lamp Watts	150

Product Data	
Order product name	Pendalyte 6.5 Perf Satin Aluminum Reflector
Order code	416SR
Material Nr. (12NC)	LIGU60001605
Commercial Code	416SR
Catalog Number Description	Pendalyte 6.5 Perf Satin Aluminum Reflector
Quick Ship	-