



LSW

TCeiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, wo lamp 54 watt T5 48" length luminaire

TCeiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, wo lamp 54 watt T5 48" length luminaire

Product data

General Information	
Lamp Watts	54
Lamp Envelope Code	T-5
Number of Lamps	2
Mounting	Wall Surface
Operating and Electrical	
Voltages	277 V
Mechanical and Housing	
Fixture Size	48 in

Product Data	
Order product name	TCeiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, wo lamp 54 watt T5 48" length luminaire
Commercial Code	LS4R254UNV-1/2-EB
Order code	LS4R254UNV-1/2-EB
Catalog Number Description	TCeiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, wo lamp 54 watt T5 48" length luminaire
Service / Spec Smart	Spec Smart (10 Days) USA
Material Nr. (12NC)	LIGU60005539