



# Vetro PS Pendants

Vetro Pendant, 8W LED, 3000K CCT, Satin Aluminum, Universal Voltage 120/277V (see PS-conical or PS-cylindrical spec sheet for Glass/Acrylic options)

Vetro Pendant, 8W LED, 3000K CCT, Satin Aluminum, Universal Voltage 120/277V (see PS-conical or PS-cylindrical spec sheet for Glass/Acrylic options)

Satin machined aluminum and hand-blown opal glass. A handsome proportion of materials engineered to provide a functional design element and an efficient luminaire.  
Must order: Power Head and Glass separately.

## Product data

General Information	
Lamp Source Code	LED
Color Temperature	3000K
CRI	78
Mounting	Suspended
Operating and Electrical	
Luminaire Input Watts	6
Voltages	120/277 V
Initial Performance (IEC Compliant)	
Luminaire Lumens	104

Product Data	
Order product name	Vetro Pendant, 8W LED, 3000K CCT, Satin Aluminum, Universal Voltage 120/277V (see PS-conical or PS-cylindrical spec sheet for Glass/Acrylic options)
Commercial Code	PS01LW30SAU
Order code	PS01LW30SAU
Catalog Number Description	Vetro Pendant, 8W LED, 3000K CCT, Satin Aluminum, Universal Voltage 120/277V (see PS-conical or PS-cylindrical spec sheet for Glass/Acrylic options)
Service / Spec Smart	-
Material Nr. (12NC)	LIGU60005645