



Vetro PS Pendants

Vetro Pendant,, 13W CFL 4-pin twin tube (Dulux S/E 2Gx7) Satin Aluminum, 277V (see PS-conical or PS-cylindrical spec sheet for Glass/Acrylic options)

Vetro Pendant,, 13W CFL 4-pin twin tube (Dulux S/E 2Gx7) Satin Aluminum, 277V (see PS-conical or PS-cylindrical spec sheet for Glass/Acrylic options)

Satin machined aluminum and hand-blown opal glass. A handsome proportion of materials engineered to provide a functional design element and an efficient luminaire.

Must order: Power Head and Glass separately.

Product data

General Information		Commercial Code	PS132SA
Lamp Source Code	CFL	Order code	PS132SA
Lamp Watts	13	Catalog Number Description	Vetro Pendant,, 13W CFL 4-pin twin tube (Dulux S/E 2Gx7) Satin Aluminum, 277V (see PS-conical or PS-cylindrical spec sheet for Glass/Acrylic options)
Lamp Envelope Code	Twin T	Service / Spec Smart	-
Number of Lamps	1	Material Nr. (12NC)	LIGU60005649
Mounting	Suspended		
Operating and Electrical			
Maximum Lamp Watts	13		
Voltages	277 V		
Product Data			
Order product name	Vetro Pendant,, 13W CFL 4-pin twin tube (Dulux S/E 2Gx7) Satin Aluminum, 277V (see PS-conical or PS-cylindrical spec sheet for Glass/Acrylic options)		