



Vetro PW Series Wall Sconces

Vetro Wall Sconce, 13W CFL 4-pin twin tube (Dulux S/E 2Gx7) Satin Aluminum, 120V (see PW spec sheet for Glass/Acrylic options)

Vetro Wall Sconce, 13W CFL 4-pin twin tube (Dulux S/E 2Gx7) Satin Aluminum, 120V (see PW spec sheet for Glass/Acrylic options)

Satin machined aluminum and hand-blown opal glass. A handsome proportion of materials engineered to provide a functional design element and an efficient luminaire.
Must order: Power Head and Glass separately.

Product data

General Information		Commercial Code	PW13SA
Lamp Source Code	CFL	Order code	PW13SA
Lamp Watts	13	Catalog Number Description	Vetro Wall Sconce, 13W CFL 4-pin twin tube (Dulux S/E 2Gx7) Satin Aluminum, 120V (see PW spec sheet for Glass/Acrylic options)
Lamp Envelope Code	Twin T	Service / Spec Smart	-
Number of Lamps	1	Material Nr. (12NC)	LIGU60005724
Mounting	Wall		
Operating and Electrical			
Maximum Lamp Watts	13		
Voltages	120 V		
Product Data			
Order product name	Vetro Wall Sconce, 13W CFL 4-pin twin tube (Dulux S/E 2Gx7) Satin Aluminum, 120V (see PW spec sheet for Glass/Acrylic options)		