



Spot LED Recessed Multiple

Spot LED 15.5W, Recessed Lighting, Frame-in kit with 3000K Fixture, Flood Reflector, Matte Black, 2 head

Spot LED 15.5W, Recessed Lighting, Frame-in kit with 3000K Fixture, Flood Reflector, Matte Black, 2 head

Spot LED recessed is a two-part system which offers a high-performing architectural approach to demanding accent lighting needs. Multiple heads provide flexibility to both harness and focus light in the built environment.

Product data

General Information	
Lamp Source Code	LED
Number of Lamps	2
Color Temperature	3000K
CRI	85
Photometric Distribution Type	Flood
Mounting	Recessed
Mechanical and Housing	
Aperture Size Code	5 1/2 in
Shape	Round
Initial Performance (IEC Compliant)	
Luminaire Lumens	1000

Product Data	
Order product name	Spot LED 15.5W, Recessed Lighting, Frame-in kit with 3000K Fixture, Flood Reflector, Matte Black, 2 head
Commercial Code	LLABR17BK030H2RFVA
Order code	LLABR17BK030H2RFVA
Catalog Number Description	Spot LED 15.5W, Recessed Lighting, Frame-in kit with 3000K Fixture, Flood Reflector, Matte Black, 2 head
Service / Spec Smart	-
Material Nr. (12NC)	LIGU60010718