



SlimSurface LED Downlight

SlimSurface LED downlight, 7-inch round, surface mount, 80 CRI, 3000K CCT, 1000 lm, 120V, Standard (TRIAC) dimming, wet location, Aluminum Finish

SlimSurface LED downlight, 7-inch round, surface mount, 80 CRI, 3000K CCT, 1000 lm, 120V, Standard (TRIAC) dimming, wet location, Aluminum Finish - 71 lm/W

SlimSurface LED is a low profile downlight intended for ceiling or wall mount applications. This 0.625" thick luminaire offers the appearance of a recessed downlight but is actually surface mounted.

Product data

General Information		Shape	
Lamp Source Code	LED	Round	
Color Temperature	3000K		
CRI	80	Initial Performance (IEC Compliant)	
Downlight Type	Open Downlight	Luminaire Lumens	1000
Photometric Distribution Type	Direct	Efficacy	71 lm/W
Mounting	Surface Wall	Product Data	
Operating and Electrical		Order product name	SlimSurface LED downlight, 7-inch round, surface mount, 80 CRI, 3000K CCT, 1000 lm, 120V, Standard (TRIAC) dimming, wet location, Aluminum Finish
Luminaire Input Watts	14	Commercial Code	S7R830K10AL
Voltages	120 V	Order code	S7R830K10AL
Mechanical and Housing			
Aperture Size Code	7 in		

SlimSurface LED Downlight

Catalog Number	Description
	SlimSurface LED downlight, 7-inch round, surface mount, 80 CRI, 3000K CCT, 1000 lm,120V, Standard (TRIAC) dimming, wet location, Aluminum Finish
Service / Spec Smart	Spec Smart (10 Days) USA

Material Nr. (12NC)	LIGU60011119
---------------------	--------------

