



# SlimSurface LED Downlight

SlimSurface LED downlight, 4-inch square, surface mount, 80 CRI, 2700K CCT, 650 lm, 120V, Standard (TRIAC) dimming, wet location, Aluminum Finish

SlimSurface LED downlight, 4-inch square, surface mount, 80 CRI, 2700K CCT, 650 lm, 120V, Standard (TRIAC) dimming, wet location, Aluminum Finish

SlimSurface LED is a low profile downlight intended for ceiling or wall mount applications. This 0.625" thick luminaire offers the appearance of a recessed downlight but is actually surface mounted.

## Product data

<b>General Information</b>		<b>Shape</b>	
Lamp Source Code	LED	Square	
Color Temperature	2700K		
CRI	80	<b>Initial Performance (IEC Compliant)</b>	
Downlight Type	Open Downlight	Luminaire Lumens	
Photometric Distribution Type	Direct	650	
Mounting	Surface Wall		
<b>Operating and Electrical</b>		<b>Product Data</b>	
Luminaire Input Watts	10	Order product name	
Voltages	120 V	SlimSurface LED downlight, 4-inch square, surface mount, 80 CRI, 2700K CCT, 650 lm, 120V, Standard (TRIAC) dimming, wet location, Aluminum Finish	
<b>Mechanical and Housing</b>		Commercial Code	
Aperture Size Code	4 in	S4S827K7AL	
		Order code	
		S4S827K7AL	
		Catalog Number Description	
		SlimSurface LED downlight, 4-inch square, surface mount, 80 CRI, 2700K CCT, 650 lm, 120V, Standard (TRIAC) dimming, wet location, Aluminum Finish	

SlimSurface LED Downlight

Service / Spec Smart	Spec Smart (10 Days) USA
Material Nr. (12NC)	LIGU60011123

