



Alcyon Line Voltage

Alcyon PAR20 Ring, Black

Alcyon PAR20 Ring, Black

Alcyon Low and Line Voltage luminaires utilize today's reliable and economical halogen and Incandescent lamps for ambient, task, accent and wall washing applications. Available in PAR20, PAR30, PAR38 and T4 halogen sources, Alcyon delivers bright light that is easily dimmable.

Product data

General Information

Lamp Source Code	HALLV
Lamp Envelope Code	PAR-20
Number of Lamps	1
Mounting	Track

Operating and Electrical

Voltages	120/277 V
----------	-----------

Product Data

Order product name	Alcyon PAR20 Ring, Black
Commercial Code	22OR2BK
Order code	22OR2BK
Catalog Number Description	Alcyon PAR20 Ring, Black
Service / Spec Smart	-
Material Nr. (12NC)	LIGU60011199