



# Evolution MR16 4"

## 4 1/2" Evolution 2" Pinhole MR16

### 4 1/2" Evolution 2" Pinhole MR16

Recessed adjustable downlights provide accent and task lighting or downlighting in sloped ceilings using low voltage MR-16 lamps available in a wide variety of wattages and beam spreads. 2" aperture pinhole reflector (C4MR2) match other Evolution downlights.

#### Product data

General Information	
Lamp Watts	37/42/50/75
Lamp Envelope Code	MR-16
Number of Lamps	1
Downlight Type	Accent Adjustable
Mounting	Recessed franse vertaling
Operating and Electrical	
Maximum Lamp Watts	75
Mechanical and Housing	
Aperture Size Code	4 1/2 in

Shape	Round
Product Data	
Order product name	4 1/2" Evolution 2" Pinhole MR16
Commercial Code	C4MR2BKW
Order code	C4MR2BKW
Catalog Number Description	4 1/2" Evolution 2" Pinhole MR16
Service / Spec Smart	-
Material Nr. (12NC)	LIGU60012683