



Evolution Frame-In Kit

4 1/2" Evolution Frame Air Seal Ic MR16

4 1/2" Evolution Frame Air Seal Ic MR16

Energy efficient frames designed for residential applications, CSA certified for direct contact with insulation. For installation in plaster or drywall ceilings up to 1" thick. luminaires come complete with swivel locking mounting bars for easy installation.

Product data

General Information	
Lamp Watts	37/50
Lamp Envelope Code	MR-16
Number of Lamps	1
Downlight Type	Open Downlight
Mounting	Recessed franse vertaling
Operating and Electrical	
Maximum Lamp Watts	50
Voltages	120 V
Mechanical and Housing	
Aperture Size Code	4 1/2 in

Shape	Round
Product Data	
Order product name	4 1/2" Evolution Frame Air Seal Ic MR16
Commercial Code	C4AICLVM1
Order code	C4AICLVM1
Catalog Number Description	4 1/2" Evolution Frame Air Seal Ic MR16
Service / Spec Smart	-
Material Nr. (12NC)	LIGU60012733