



Lytejacks Track Heads

Lyteacks Sof-Tech Open Ring 50W MR16 Black

Lyteacks Sof-Tech Open Ring 50W MR16 Black

A complete LyteJack consists of a decorative Style Jack Shade, a Lytedrop (with a 20W or 35W halogen lamp), and a Power Jack. Please specify and order each separately based on the ordering guide below. See specification sheet for details on compatibility.

Product data

General Information	
Lamp Source Code	HALLV
Lamp Envelope Code	MR-16
Number of Lamps	1
Photometric Distribution Type	Spot
Mounting	Track
Operating and Electrical	
Voltages	120/277 V

Product Data	
Order product name	Lyteacks Sof-Tech Open Ring 50W MR16 Black
Commercial Code	8675BBK
Order code	8675BBK
Catalog Number Description	Lyteacks Sof-Tech Open Ring 50W MR16 Black
Service / Spec Smart	-
Material Nr. (12NC)	LIGU60012830