



# Mini HID Track Heads

## HID Ring PAR30 70W ELE M/BK

### HID Ring PAR30 70W ELE M/BK

CMH luminaires offer up to 70% energy savings vs. incandescent spotlights with 3 to 4 times longer lamp life. Lytespan Mini HID is the choice for high-performance energy smart retail and architectural lighting.

#### Product data

General Information	
Lamp Envelope Code	PAR-30
Number of Lamps	1
Mounting	Track
Operating and Electrical	
Voltages	120/277 V
Product Data	
Order product name	HID Ring PAR30 70W ELE M/BK

Commercial Code	8107BK
Order code	8107BK
Catalog Number Description	HID Ring PAR30 70W ELE M/BK
Service / Spec Smart	-
Material Nr. (12NC)	LIGU60012918