



Mini HID Track Heads

HID Ring PAR30 70W ELE M/WH

HID Ring PAR30 70W ELE M/WH

CMH luminaires offer up to 70% energy savings vs. incandescent spotlights with 3 to 4 times longer lamp life. Lytespan Mini HID is the choice for high-performance energy smart retail and architectural lighting.

Product data

General Information		Commercial Code	8107WH
Lamp Envelope Code	PAR-30	Order code	8107WH
Number of Lamps	1	Catalog Number Description	HID Ring PAR30 70W ELE M/WH
Mounting	Track	Service / Spec Smart	-
Operating and Electrical		Material Nr. (12NC)	LIGU60012919
Voltages	120/277 V		
Product Data			
Order product name	HID Ring PAR30 70W ELE M/WH		