



Mini HID Track Heads

Mini HID 70W CMH T4.5 G8.5Wall Washer Black with Matte Aluminum Specular Reflector

Mini HID 70W CMH T4.5 G8.5Wall Washer Black with Matte Aluminum Specular Reflector

CMH luminaires offer up to 70% energy savings vs. incandescent spotlights with 3 to 4 times longer lamp life. Lytespan Mini HID is the choice for high-performance energy smart retail and architectural lighting.

Product data

General Information	
Lamp Envelope Code	T-4.5
Number of Lamps	1
Photometric Distribution Type	Wide Flood
Mounting	Track
Operating and Electrical	
Voltages	120/277 V
Product Data	
Order product name	Mini HID 70W CMH T4.5 G8.5Wall Washer Black with Matte Aluminum Specular Reflector

Commercial Code	81F70T45SPCBK
Order code	81F70T45SPCBK
Catalog Number Description	Mini HID 70W CMH T4.5 G8.5Wall Washer Black with Matte Aluminum Specular Reflector
Service / Spec Smart	-
Material Nr. (12NC)	LIGU60013012