



LyteProfile LED

4" LyteProfile Light Engine 80 CRI 3500K

4" LyteProfile Light Engine 80 CRI 3500K

LyteProfile LED downlights are designed for new construction and include downlight and wall wash distributions. They are highly energy efficient with up to 100 lm/w, provide a full 60 degree cutoff, and feature an impressively shallow 4.5" housing.

Product data

| General Information | |
|------------------------|----------------|
| Color Temperature | 3500K |
| CRI | 80 |
| Downlight Type | Open Downlight |
| Mounting | Recessed |
| Mechanical and Housing | |
| Aperture Size Code | 4 in |
| Shape | Round |

| Product Data | |
|----------------------------|--|
| Order product name | 4" LyteProfile Light Engine 80 CRI 3500K |
| Commercial Code | P4RD835VB |
| Order code | P4RD835VB |
| Catalog Number Description | 4" LyteProfile Light Engine 80 CRI 3500K |
| Service / Spec Smart | - |
| Material Nr. (12NC) | LIGU60013329 |