



# SlimSurface LED Downlight

SlimSurface LED downlight, 5-inch round, surface mount, 80 CRI, 3500K CCT, 650 lm, 120V, Standard (TRIAC) dimming, wet location, Aluminum Finish

SlimSurface LED downlight, 5-inch round, surface mount, 80 CRI, 3500K CCT, 650 lm, 120V, Standard (TRIAC) dimming, wet location, Aluminum Finish

SlimSurface LED is a low profile downlight intended for ceiling or wall mount applications. This 0.625" thick luminaire offers the appearance of a recessed downlight but is actually surface mounted.

## Product data

<b>General Information</b>		<b>Shape</b>	
Lamp Source Code	LED	Round	
Colour Temperature	3500K		
CRI	80	<b>Initial Performance (IEC Compliant)</b>	
Downlight Type	Open Downlight	Luminaire Lumens	
Photometric Distribution Type	Direct	650	
Mounting	Surface Wall		
<b>Operating and Electrical</b>		<b>Product Data</b>	
Luminaire Input Watts	10	Order product name	
Voltages	120 V	SlimSurface LED downlight, 5-inch round, surface mount, 80 CRI, 3500K CCT, 650 lm, 120V, Standard (TRIAC) dimming, wet location, Aluminum Finish	
<b>Mechanical and Housing</b>		Commercial Code	
Aperture Size Code	5 in	S5R835K7AL	
		Order code	
		S5R835K7AL	
		Catalog Number Description	
		SlimSurface LED downlight, 5-inch round, surface mount, 80 CRI, 3500K CCT, 650 lm, 120V, Standard (TRIAC) dimming, wet location, Aluminum Finish	

SlimSurface LED Downlight

Service / Spec Smart	-
Material Nr. (12NC)	LIGU60013805

