



SlimSurface LED Downlight

SlimSurface LED downlight, 6-inch square surface mount, 80 CRI, 4000K CCT, 1000 lm, 120V, Standard (TRIAC) dimming, wet location, Matte White Finish

SlimSurface LED downlight, 6-inch square surface mount, 80 CRI, 4000K CCT, 1000 lm, 120V, Standard (TRIAC) dimming, wet location, Matte White Finish

SlimSurface LED is a low profile downlight intended for ceiling or wall mount applications. This 0.625" thick luminaire offers the appearance of a recessed downlight but is actually surface mounted.

Product data

General Information		Shape	
Lamp Source Code	LED	Square	
Colour Temperature	4000K		
CRI	80		
Downlight Type	Open Downlight		
Photometric Distribution Type	Direct		
Mounting	Surface Wall		
Operating and Electrical		Initial Performance (IEC Compliant)	
Luminaire Input Watts	14	Luminaire Lumens	1000
Voltages	120 V		
Mechanical and Housing		Product Data	
Aperture Size Code	6 in	Order product name	SlimSurface LED downlight, 6-inch square surface mount, 80 CRI, 4000K CCT, 1000 lm, 120V, Standard (TRIAC) dimming, wet location, Matte White Finish
		Commercial Code	S6S840K10
		Order code	S6S840K10
		Catalog Number Description	SlimSurface LED downlight, 6-inch square surface mount, 80 CRI, 4000K CCT, 1000 lm, 120V, Standard (TRIAC) dimming, wet location, Matte White Finish

SlimSurface LED Downlight

Service / Spec Smart	-
Material Nr. (12NC)	LIGU60013810

