



SlimSurface LED Downlight

SlimSurface LED downlight, 7-inch round, surface mount, 80 CRI, 3500K CCT, 1000 lm,120V, Standard (TRIAC) dimming, wet location, Aluminum Finish

SlimSurface LED downlight, 7-inch round, surface mount, 80 CRI, 3500K CCT, 1000 lm,120V, Standard (TRIAC) dimming, wet location, Aluminum Finish

SlimSurface LED is a low profile downlight intended for ceiling or wall mount applications. This 0.625" thick luminaire offers the appearance of a recessed downlight but is actually surface mounted.

Product data

General Information	
Lamp Source Code	LED
Colour Temperature	3500K
CRI	80
Downlight Type	Open Downlight
Photometric Distribution Type	Direct
Mounting	Surface Wall

Operating and Electrical	
Voltages	120 V
Luminaire Input Watts	14

Mechanical and Housing	
Aperture Size Code	7 in
Shape	Round

Initial Performance (IEC Compliant)	
Luminaire Lumens	1000

Product Data	
Order product name	SlimSurface LED downlight, 7-inch round, surface mount, 80 CRI, 3500K CCT, 1000 lm,120V, Standard (TRIAC) dimming, wet location, Aluminum Finish
Order code	S7R835K10AL

SlimSurface LED Downlight

Material Nr. (12NC)	LIGU60013813
Catalog Number	S7R835K10AL
Catalog Number Description	SlimSurface LED downlight, 7-inch round, surface mount, 80 CRI, 3500K CCT, 1000 lm,120V, Standard (TRIAC) dimming, wet location, Aluminum Finish

