



SlimSurface LED Downlight

SlimSurface LED downlight, 7-inch round, surface mount, 80 CRI, 4000K CCT, 1000 lm, 120V, Standard (TRIAC) dimming, wet location, Aluminum Finish

SlimSurface LED downlight, 7-inch round, surface mount, 80 CRI, 4000K CCT, 1000 lm, 120V, Standard (TRIAC) dimming, wet location, Aluminum Finish

SlimSurface LED is a low profile downlight intended for ceiling or wall mount applications. This 0.625" thick luminaire offers the appearance of a recessed downlight but is actually surface mounted.

Product data

General Information		Shape	
Lamp Source Code	LED	Round	
Color Temperature	4000K		
CRI	80	Initial Performance (IEC Compliant)	
Downlight Type	Open Downlight	Luminaire Lumens	
Photometric Distribution Type	Direct	1000	
Mounting	Surface Wall		
Operating and Electrical		Product Data	
Luminaire Input Watts	14	Order product name	SlimSurface LED downlight, 7-inch round, surface mount, 80 CRI, 4000K CCT, 1000 lm, 120V, Standard (TRIAC) dimming, wet location, Aluminum Finish
Voltages	120 V	Commercial Code	S7R840K10AL
Mechanical and Housing		Order code	S7R840K10AL
Aperture Size Code	7 in	Catalog Number Description	SlimSurface LED downlight, 7-inch round, surface mount, 80 CRI, 4000K CCT, 1000 lm, 120V, Standard (TRIAC) dimming, wet location, Aluminum Finish

SlimSurface LED Downlight

Service / Spec Smart	Spec Smart (10 Days) USA
Material Nr. (12NC)	LIGU60013815

