



# SlimSurface LED Downlight

SlimSurface LED downlight, 6-inch square surface mount, 80 CRI, 3000K CCT, 1000 lm, 120V, Standard (TRIAC) dimming, wet location, Black Finish

SlimSurface LED downlight, 6-inch square surface mount, 80 CRI, 3000K CCT, 1000 lm, 120V, Standard (TRIAC) dimming, wet location, Black Finish

SlimSurface LED is a low profile downlight intended for ceiling or wall mount applications. This 0.625" thick luminaire offers the appearance of a recessed downlight but is actually surface mounted.

## Product data

<b>General Information</b>		<b>Shape</b>	
Lamp Source Code	LED	Square	
Color Temperature	3000K		
CRI	80	<b>Initial Performance (IEC Compliant)</b>	
Downlight Type	Open Downlight	Luminaire Lumens	
Photometric Distribution Type	Direct	1000	
Mounting	Surface Wall		
<b>Operating and Electrical</b>		<b>Product Data</b>	
Luminaire Input Watts	14	Order product name	
Voltages	120 V	SlimSurface LED downlight, 6-inch square surface mount, 80 CRI, 3000K CCT, 1000 lm, 120V, Standard (TRIAC) dimming, wet location, Black Finish	
<b>Mechanical and Housing</b>		Commercial Code	
Aperture Size Code	6 in	S6S830K10BK	
		Order code	
		S6S830K10BK	
		Catalog Number Description	
		SlimSurface LED downlight, 6-inch square surface mount, 80 CRI, 3000K CCT, 1000 lm, 120V, Standard (TRIAC) dimming, wet location, Black Finish	

SlimSurface LED Downlight

Service / Spec Smart	Spec Smart (10 Days) USA
Material Nr. (12NC)	LIGU60013825

