



# LyteCaster LED Downlight

## LyteCaster LED 5" Downlight Light Engine 1000 lm, 80 CRI, 4000K

LyteCaster LED 5" Downlight Light Engine 1000 lm, 80 CRI, 4000K

Philips Lightolier LyteCaster LED Downlight and Adjustable luminaires provide comfortable, quality illumination for new construction and renovation spaces. LyteCaster's shallow height and modular design make it a versatile lighting option. It is available in 4" (650 lm&1000lm), 5" (1000 lm&1500lm), and 6" (1500 lm&2000lm) aperture sizes. The 5" is also available with a warm glow dimming effect from 2700K-2200K that delivers 700 lm.

### Product data

General Information	
Colour Temperature	4000K
CRI	80
Downlight Type	Open Downlight
Mounting	Recessed franse vertaling
Mechanical and Housing	
Aperture Size Code	5 in
Shape	Round
Initial Performance (IEC Compliant)	
Luminaire Lumens	1000

Product Data	
Order product name	LyteCaster LED 5" Downlight Light Engine 1000 lm, 80 CRI, 4000K
Commercial Code	L5R10840VA
Order code	L5R10840VA
Catalog Number Description	LyteCaster LED 5" Downlight Light Engine 1000 lm, 80 CRI, 4000K
Service / Spec Smart	-
Material Nr. (12NC)	LIGU60013910