



LyteCaster LED Downlight

LyteCaster LED 5" Adjustable Light Engine/Trim 1000lm, 90 CRI, 2700K

LyteCaster LED 5" Adjustable Light Engine/Trim 1000lm, 90 CRI, 2700K

Philips Lightolier LyteCaster LED Downlight and Adjustable luminaires provide comfortable, quality illumination for new construction and renovation spaces. LyteCaster's shallow height and modular design make it a versatile lighting option. It is available in 4" (650 lm&1000lm), 5" (1000 lm&1500lm), and 6" (1500 lm&2000lm) aperture sizes. The 5" is also available with a warm glow dimming effect from 2700K-2200K that delivers 700 lm.

Product data

General Information	
Colour Temperature	2700K
CRI	90
Downlight Type	Accent Adjustable
Mounting	Recessed franse vertaling
Mechanical and Housing	
Aperture Size Code	5 in
Shape	Round
Initial Performance (IEC Compliant)	
Luminaire Lumens	1000

Product Data	
Order product name	LyteCaster LED 5" Adjustable Light Engine/Trim 1000lm, 90 CRI, 2700K
Commercial Code	L5RA10927WVA
Order code	L5RA10927WVA
Catalog Number Description	LyteCaster LED 5" Adjustable Light Engine/Trim 1000lm, 90 CRI, 2700K
Service / Spec Smart	-
Material Nr. (12NC)	LIGU60013915