



# LyteCaster LED Downlight

## LyteCaster LED 6" Downlight Light Engine 1500 lm, 90 CRI, 2700K

LyteCaster LED 6" Downlight Light Engine 1500 lm, 90 CRI, 2700K

Philips Lightolier LyteCaster LED Downlight and Adjustable luminaires provide comfortable, quality illumination for new construction and renovation spaces. LyteCaster's shallow height and modular design make it a versatile lighting option. It is available in 4" (650 lm&1000lm), 5" (1000 lm&1500lm), and 6" (1500 lm&2000lm) aperture sizes. The 5" is also available with a warm glow dimming effect from 2700K-2200K that delivers 700 lm.

### Product data

General Information	
Color Temperature	2700K
CRI	90
Downlight Type	Open Downlight
Mounting	Recessed
Mechanical and Housing	
Aperture Size Code	6 in
Shape	Round
Initial Performance (IEC Compliant)	
Luminaire Lumens	1500

Product Data	
Order product name	LyteCaster LED 6" Downlight Light Engine 1500 lm, 90 CRI, 2700K
Commercial Code	L6R15927VA
Order code	L6R15927VA
Catalog Number Description	LyteCaster LED 6" Downlight Light Engine 1500 lm, 90 CRI, 2700K
Service / Spec Smart	Service Smart (2 Days) USA
Material Nr. (12NC)	LIGU60013924