



LyteCaster LED Downlight

LyteCaster LED 4" Adjustable Light Engine/Trim 650lm, 80 CRI, 3000K

LyteCaster LED 4" Adjustable Light Engine/Trim 650lm, 80 CRI, 3000K

Philips Lightolier LyteCaster LED Downlight and Adjustable luminaires provide comfortable, quality illumination for new construction and renovation spaces. LyteCaster's shallow height and modular design make it a versatile lighting option. It is available in 4" (650 lm&1000lm), 5" (1000 lm&1500lm), and 6" (1500 lm&2000lm) aperture sizes. The 5" is also available with a warm glow dimming effect from 2700K-2200K that delivers 700 lm.

Product data

General Information	
Color Temperature	3000K
CRI	80
Downlight Type	Accent Adjustable
Mounting	Recessed
Mechanical and Housing	
Aperture Size Code	4 in
Shape	Round
Initial Performance (IEC Compliant)	
Luminaire Lumens	650

Product Data	
Order product name	LyteCaster LED 4" Adjustable Light Engine/Trim 650lm, 80 CRI, 3000K
Commercial Code	L4RA06830WVA
Order code	L4RA06830WVA
Catalog Number Description	LyteCaster LED 4" Adjustable Light Engine/Trim 650lm, 80 CRI, 3000K
Service / Spec Smart	-
Material Nr. (12NC)	LIGU60013997