



# LyteCaster LED Downlight

## LCA LED 6" MODULE 80 CRI 30K 2000LM

### LCA LED 6" - MODULE 80 CRI 30K 2000LM

Philips Lightolier LyteCaster LED Downlight and Adjustable luminaires provide comfortable, quality illumination for new construction and renovation spaces. LyteCaster's shallow height and modular design make it a versatile lighting option. It is available in 4" (650 lm&1000lm), 5" (1000 lm&1500lm), and 6" (1500 lm&2000lm) aperture sizes. The 5" is also available with a warm glow dimming effect from 2700K-2200K that delivers 700 lm.

#### Product data

General Information	
Color Temperature	3000K
CRI	80
Downlight Type	Open Downlight
Mounting	Recessed
Mechanical and Housing	
Aperture Size Code	6 in
Shape	Round
Initial Performance (IEC Compliant)	
Luminaire Lumens	2000

Product Data	
Order product name	LCA LED 6" MODULE 80 CRI 30K 2000LM
Commercial Code	L6R20830VA
Order code	L6R20830VA
Catalog Number Description	LCA LED 6" MODULE 80 CRI 30K 2000LM
Service / Spec Smart	-
Material Nr. (12NC)	LIGU60014220