



# Retrofit downlight

## Retrofit downlight 4" Rd 900lm 90 30K 120V

Retrofit downlight 4" Rd 900lm 90 30K 120V

Philips Lightolier LED Retrofit downlight is your go-to LED replacement solution. Whether you have a commercial, institutional or residential space that needs an energy saving upgrade, the Retrofit downlight will be the fast and cost-effective answer.

### Product data

General Information	
Lamp Source Code	LED
Colour Temperature	3000K
CRI	90
Downlight Type	Open Downlight
Mounting	Recessed franse vertaling
Operating and Electrical	
Voltages	120 V
Mechanical and Housing	
Shape	Round

Initial Performance (IEC Compliant)	
Luminaire Lumens	900
Product Data	
Order product name	Retrofit downlight 4" Rd 900lm 90 30K 120V
Commercial Code	RD4R089301W
Order code	RD4R089301W
Catalog Number Description	Retrofit downlight 4" Rd 900lm 90 30K 120V
Service / Spec Smart	Service Smart (2 Days) North America
Material Nr. (12NC)	LIGU60014751