



# CorePro LED Mini Cylinder

CorePro LED Mini Cylinder, 900 lm, 35° Wide Flood, 80 CRI / 3000K CCT, Matte Aluminum Finish

CorePro LED Mini Cylinder, 900 lm, 35° Wide Flood, 80 CRI / 3000K CCT, Matte Aluminum Finish

The Philips Lightolier CorePro LED Mini Cylinder is a completely integrated LED luminaire. By combining the optics, light source, thermal management system and driver into a single housing, this luminaire provides a sleek look suitable for lower mounting heights and smaller spaces. This small, sleek luminaire design offers efficacy up to 80lm/w.

## Product data

General Information		Initial Performance (IEC Compliant)	
Lamp Source Code	LED	Luminaire Lumens	900
Lamp Watts	9		
Colour Temperature	3000K		
CRI	80		
Downlight Type	Cylinders		
Mounting	Track		
Operating and Electrical		Product Data	
Voltages	120 V	Order product name	CorePro LED Mini Cylinder, 900 lm, 35° Wide Flood, 80 CRI / 3000K CCT, Matte Aluminum Finish
		Commercial Code	LT08RWF830ALVA
		Order code	LT08RWF830ALVA
		Catalog Number Description	CorePro LED Mini Cylinder, 900 lm, 35° Wide Flood, 80 CRI / 3000K CCT, Matte Aluminum Finish
		Service / Spec Smart	-
		Material Nr. (12NC)	LIGU60014770
Mechanical and Housing			
Aperture Size Code	1 3/4 in		