



LyteCaster LED Downlight

LCA LED 4" MODULE 90 CRI 30K 1000LM

LCA LED 4" - MODULE 90 CRI 30K 1000LM

Philips Lightolier LyteCaster LED Downlight and Adjustable luminaires provide comfortable, quality illumination for new construction and renovation spaces. LyteCaster's shallow height and modular design make it a versatile lighting option. It is available in 4" (650 lm&1000lm), 5" (1000 lm&1500lm), and 6" (1500 lm&2000lm) aperture sizes. The 5" is also available with a warm glow dimming effect from 2700K-2200K that delivers 700 lm.

Product data

General Information	
Color Temperature	3000K
CRI	90
Downlight Type	Open Downlight
Mounting	Recessed
Mechanical and Housing	
Aperture Size Code	4 in
Initial Performance (IEC Compliant)	
Luminaire Lumens	1000

Product Data	
Order product name	LCA LED 4" MODULE 90 CRI 30K 1000LM
Commercial Code	L4R10930VA
Order code	L4R10930VA
Catalog Number Description	LCA LED 4" MODULE 90 CRI 30K 1000LM
Service / Spec Smart	-
Material Nr. (12NC)	LIGU60014794