



Sof-Tech Line Voltage Track Heads

Sof-Tech Rings 75W PAR30 Black

Sof-Tech Rings 75W PAR30 Black

Sof-Tech features die cast components with silicone rubber for aiming comfort. This series is available in both open back or fully enclosed versions, and two accessories may be used with the appropriate accessory holder.

Product data

General Information	
Lamp Envelope Code	PAR-30
Lamp Source Code	Halogen Low Voltage
Number of Lamps	1
Photometric Distribution Type	Medium
Mounting	Track
Operating and Electrical	
Voltages	120/277 V

Product Data	
Order product name	Sof-Tech Rings 75W PAR30 Black
Order code	8330BK
Material Nr. (12NC)	LIGU60014829
Commercial Code	8330BK
Catalog Number Description	Sof-Tech Rings 75W PAR30 Black
Quick Ship	Service Smart (2 Days) USA